

ידית מגנט (סב בלבד) - VBM TOH / TOV



TOV



TOH


מערכות VBM מדגם TOH ומדגם TOV מאפשרות הטיה של השלבים ללא הרמה והורדה באמצעות ידית מגנט. המערכות מעניקות מענה מושלם למבני ציבור, בתי חולים, מבני ממשלה ומשרדים. זאת, בזכות העמידות הגבוהה של המוצר.

בדגם TOV ממוקמת ידית המגנט מצידה הימני או השמאלי של יחידת הזכוכית, בצמוד לדופן פרופיל הפתח. הטיית השלבים נעשית על ידי הזזת ידית המגנט מטה ומעלה.

בדגם TOH ממוקמת ידית המגנט בצורה אופקית, בצמוד לפרופיל העליון או התחתון של החלון. הטיית השלבים נעשית על ידי הסטת ידית מגנט ימינה ושמאלה.

מרווחי אוויר: 18 מ"מ, 20 מ"מ, 25 מ"מ, 27 מ"מ.


VBM TOV 18mm - Detailed dimensions (mm)




Section A-A




Section B-B




Section C-C




Section D-D



Power and command socket




VBM TOV 20mm - Detailed dimensions (mm)




Section A-A




Section B-B




Section C-C




Section D-D



Power and command socket




VBM TOV 25mm - Detailed dimensions (mm)




Section A-A




Section B-B




Section C-C




Section D-D



Power and command socket




VBM TOH 18mm - Detailed dimensions (mm)




Section A-A




Section B-B




Section C-C




Section D-D



Power and command socket




VBM TOH 20mm - Detailed dimensions (mm)




Section A-A




Section B-B




Section C-C




Section D-D



Power and command socket




VBM TOH 25mm - Detailed dimensions (mm)




Section A-A




Section B-B




Section C-C



Section D-D



Power and command socket



טבלת גדלים

Height (cm)	Width (cm)																
	30	40	50	60	70	80	90	100	110	120	130	140	150	160	170	180	190
50																	
60	+	+	+	+	+	+	+	+	+	+							
70	+	+	+	+	+	+	+	+	+	+							
80	+	+	+	+	+	+	+	+	+	+	+						
90	+	+	+	+	+	+	+	+	+	+	+	+					
100	+	+	+	+	+	+	+	+	+	+	+	+	+				
110	+	+	+	+	+	+	+	+	+	+	+	+	+	+			
120	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+
130	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
140	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
150	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
160	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
170	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
180	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
190	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
200	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
210	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	
220	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	

ביחידות המסומנות בכחול עובי הזכוכית הפנימית לא יעלה על 4 מ"מ, אלא באישור כתוב מחברת אורשייד.